

# Pilkington **Mirropane T.M.** Transparent Mirror Glass





First in Glass

# Pilkington Mirropane T.M.™ Transparent Mirror Glass

Developed to provide the highest level of performance in the market (requires only an 8:1 light ratio), this glass produces the optimal mix of tint and reflectivity, perfect for enhanced security and undetected observation.



View from subject-side in a child care application.



View from observer-side.

Note: Cover image depicts actual Pilkington Mirropane T.M" Glass in use, cut-away to show observer in a focus group application.



First in Glass

Pilkington Building Products

North America

P.O. Box 799

811 Madison Ave.

Toledo, OH 43697-0799

Main Office: 419 247 3731

Sales & Technical Support: 800 221 0444

E-mail:

building.products@us.pilkington.com

Website: www.pilkington.com

Pilkington Mirropane T.M:" Transparent Mirror Glass and Optifloat" Grey Tinted Glass are trademarks of Pilkington.

Form No. 0504/7M/3444/BP ©2004 Pilkington. Printed in U.S.A.

#### **Product Description**

Ideal for surveillance, security and administrative applications, Pilkington **Mirropane T.M.**™

Transparent Mirror Glass creates a visual barrier between subjects and their observers, performing like an ordinary mirror on one side and a tinted window on the other.

#### **Product Features**

- HIGH REFLECTIVITY AND LIGHT TRANSMITTANCE allow privacy with crisp, unobtrusive vision into the observed room.
- DURABLE, PYROLYTICALLY DEPOSITED COATING offers significantly better scratch and abrasion resistance than vacuum-coated products. A transparent mirror is created by applying a reflective silver-colored coating on 1/4ý (6mm) Pilkington Optifloat<sup>™</sup> Grey Tinted Glass.
- POST HEAT-TREATABLE for maximum strength, it can be handled, cut, insulated, laminated and tempered.
- EXCELLENT AVAILABILITY for ease of inventory and replenishment. Pyrolytic coating allows for easy handling, fabrication and storage.
- AVAILABLE IN 1/4" (6mm) thickness.
- IDEAL FOR SURVEILLANCE, security in commercial settings, correctional institutions and child care businesses, hospital observation, worker monitoring and distinctive interior designs.



Cut-away view of security application.

#### **Design Considerations**

- ORIENTATION: Install transparent mirror with the reflective surface facing the brightly lit subject-side. Due to improved properties, this glass allows a wall to be completely glazed from floor to ceiling when there is no lighting on the viewing side.
- TYPE OF LIGHTING: Subject-side lighting should be bright and evenly distributed over all walls and furnishings, but should not shine directly onto the transparent mirror. Observer-side lighting should be dim with no open light sources. Opaque lamp shades are recommended for best results.
- BACKGROUND COLORS: Subject-side should be bright and light in color and shade to create a bright reflected image. Observerside décor should be subdued, non-reflective, dark and uniform.
- DISTANCES AND LIGHT LEVELS: On the observer-side, keep people, objects and light sources at a distance from the transparent mirror area. An 8:1 light ratio is recommended, with the subject-side brightly lit.
- CLEANING: Use standard glass cleaners or mild detergents. Do not use abrasives, opaque liquid cleaners, razor blades or acid-based cleaners.
- ADDITIONAL RESOURCES: Refer to Technical Bulletin ATS-125 for additional details at www.pilkington.com.

## **Vision Area Coating Quality Specifications**

The reflective coating shall meet the performance specifications as published. Coating quality will meet ASTM C 1376. A light level ratio of at least 8:1 from bright (subject) side to dark (observer) side shall be maintained for effective operation.

### Pilkington Mirropane T.M. TM Performance Data

	Nominal Glass Thickness		Glass Substrate	Visible <sup>2</sup> Transmittance	Visible <sup>2</sup> Reflectance On The Coated Side	Recommended Light Ratio	Proper Glazing
I	in.	mm	Grey	%	%	8:1 Subject-side:Observer-side	Mirror coating toward subject-side
Ī	1/4	6		11	71		

Typical values of Pilkington production are provided.

Visible data is based on laboratory spectrophotometric measurements weighted by the factors in W5\_NFRC\_2003.STD in LBNL Window 5.2 software.